

M12 T-cod 4-pol st/st m/f PUR 10m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 363 7446 100
Specification	M12 T-cod 4-pol st/st m/f PUR 10m
HARTING eCatalogue	https://b2b.harting.com/21343637446100

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 T-coding Male Straight
Connector 2	M12 T-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	4
Core structure	4x 1.5 mm ²
Coding	T-coding

Technical characteristics

Rated current	12 A
Rated voltage	63 V DC
Limiting temperature	-25 ... +80 °C
Cable diameter	7.2 mm

Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (cable)	Black
----------------	-------

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
ETIM	EC002599
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21343637446100](#)