

## M23\_12P MA,Int-thread,STR PVC cable,5M



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                             |
|--------------------|---------------------------------------------------------------------------------------------|
| Part number        | 21 37 330 0C71 050                                                                          |
| Specification      | M23_12P MA,Int-thread,STR PVC cable,5M                                                      |
| HARTING eCatalogue | <a href="https://b2b.harting.com/21373300C71050">https://b2b.harting.com/21373300C71050</a> |

### Identification

|                |                                                                                      |
|----------------|--------------------------------------------------------------------------------------|
| Category       | System cabling                                                                       |
| Series         | Circular connectors M23                                                              |
| Identification | Signal                                                                               |
| Element        | Cable assemblies                                                                     |
| Specification  | Pre-assembled on one side                                                            |
| Connector 1    | M23<br>Male Straight                                                                 |
| Type of cable  | Copper cable (round)                                                                 |
| Features       | Flame retardancy<br>Oil and UV resistant<br>Highly EMC resistant<br>Halogen freeness |

### Version

|                 |            |
|-----------------|------------|
| Cable length    | 5 m        |
| Number of cores | 12         |
| Core structure  | 12x AWG 18 |

### Technical characteristics

|                                        |                |
|----------------------------------------|----------------|
| Rated current                          | 6 A            |
| Rated voltage                          | 300 V          |
| Limiting temperature                   | -40 ... +80 °C |
| Degree of protection acc. to IEC 60529 | IP67           |



**Pushing Performance**  
Since 1945

## Material properties

|                         |                                  |
|-------------------------|----------------------------------|
| Material (contacts)     | Copper alloy                     |
| Surface (contacts)      | Silver plated                    |
| Material (cable)        | PVC                              |
| Colour (cable)          | Black                            |
| Material (overmoulding) | Thermoplastic polyurethane (TPU) |
| Colour (overmoulding)   | Black                            |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Country of origin              | China                                   |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140240889                           |
| ETIM                           | EC001855                                |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21373300C71050](#)