



Pushing Performance
Since 1945

M23_17P MA,Int-thread,STR PUR cable,10M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 330 0F72 100
Specification	M23_17P MA,Int-thread,STR PUR cable,10M
HARTING eCatalogue	https://b2b.harting.com/21373300F72100

Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Male Straight
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant Halogen freeness

Version

Cable length	10 m
Core structure	17x AWG 18

Technical characteristics

Rated current	9 A
Rated voltage	150 V
Limiting temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP67

Material properties

Material (contacts)	Copper alloy
---------------------	--------------



Pushing Performance
Since 1945

Material properties

Surface (contacts)	Silver plated
Material (cable)	PUR (polyurethane)
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240919
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21373300F72100](#)