

M23_12P FE,Int-thread,ANG PUR cable,10M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 360 0C70 100
Specification	M23_12P FE,Int-thread,ANG PUR cable,10M
HARTING eCatalogue	https://b2b.harting.com/21373600C70100

Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Female Angled
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant Halogen freeness

Version

Cable length	10 m
Number of cores	12
Core structure	12x AWG 18

Technical characteristics

Rated current	6 A
Rated voltage	300 V
Limiting temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP67



Pushing Performance
Since 1945

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (cable)	PUR (polyurethane)
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black

Commercial data

Packaging size	1
Net weight	2,000 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140241237
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21373600C70100](#)