

## M17 FE str molded 6+PE PVC open end,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 520 0703 050
Specification	M17 FE str molded 6+PE PVC open end,5m
HARTING eCatalogue	<a href="https://b2b.harting.com/21375200703050">https://b2b.harting.com/21375200703050</a>

### Identification

Category	System cabling
Series	Circular connectors M17
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M17 Overmoulded Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	7
Core structure	6x 0.5 mm <sup>2</sup> + 1 mm <sup>2</sup>

### Technical characteristics

Rated current	8 A
Rated voltage	300 V
Limiting temperature	-20 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (cable)	PVC
Colour (cable)	Black



**Pushing Performance**  
Since 1945

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240766
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21375200703050](#)