

M17 FE str molded 17p PUR open end,10m



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 520 0F02 100
Specification	M17 FE str molded 17p PUR open end,10m
HARTING eCatalogue	https://b2b.harting.com/21375200F02100

Identification

Category	System cabling
Series	Circular connectors M17
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M17 Overmoulded Female Straight
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	17
Core structure	17x AWG 22

Technical characteristics

Rated current	2 A
Rated voltage	60 V
Limiting temperature	-20 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	1,067 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240810
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21375200F02100](#)