

M12 D-cod 4-pol st/- m/- PUR PP 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 400 0445 050
Specification	M12 D-cod 4-pol st/- m/- PUR PP 5.0m
HARTING eCatalogue	https://harting.com/21404000445050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding Male Straight

Version

Cable length	5 m
Number of cores	4
Core structure	4x AWG 22/7
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Locking type	PushPull

Technical characteristics

Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Limiting temperature	-40 ... +70 °C moved -20 ... +60 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	6.5 mm ± 0.2 mm



Pushing Performance
Since 1945

Technical characteristics

Minimum bending radius	3x Cable diameter (singular bending) 7x Cable diameter (repeated bending)
Bending cycles	≥ 3.000.000

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green

Specifications and approvals

Specifications	UN/ECE-R 118
----------------	--------------

Commercial data

Packaging size	1
Net weight	356 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140490895
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21404000445050](#)