

## FO CA LCdx-LCdx 2E9/125 G657.A1, 8.0m




Image is for illustration purposes only. Please refer to product description.

Part number	33 01 241 0080 008
Specification	FO CA LCdx-LCdx 2E9/125 G657.A1, 8.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/33012410080008">https://b2b.harting.com/33012410080008</a>

### Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	LC duplex
Connector 2	LC duplex
Type of cable	FO cable
Description of the cable	Singlemode

### Version

Cable length	8 m
Number of fibres	2
Fiber type	2E9/125 G657.A1

### Technical characteristics

Cable diameter	5.17 mm
----------------	---------

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	8a5c37c3-d5dc-469f-b994-a066c654819f
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Latvia
European customs tariff number	85447000
GTIN	5713140149540
eCl@ss	27061003 Patch cable fiber-optic

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33012410080008](#)