

Han 1A OM 12 Pole +latch f/ - PVC 5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 40 110 0703 050
Specification	Han 1A OM 12 Pole +latch f/ - PVC 5m
HARTING eCatalogue	https://b2b.harting.com/33401100703050

Identification

Category	System cabling
Series	Han® 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han® 1A Female Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

Version

Cable length	5 m
Number of cores	12
Core structure	12x 0.5 mm ²
Number of contacts	12
Locking type	Snap-in latches
Details	IP66 / IP67 in mated cable to cable position

Technical characteristics

Rated current	6.5 A
Rated voltage	50 V
Limiting temperature	-40 ... +80 °C unmoved -5 ... +80 °C moved
Mating cycles	≥100



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP66 mated condition
	IP67 mated condition
Cable diameter	8.7 mm

Material properties

Material (cable)	PVC
Colour (cable)	Grey

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
eCl@ss	27060311 Assembled sensor actuator-line

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

33401100703050