

## ix Type B solder 10xAWG26 PUR 2.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 161 6A21 020
Specification	ix Type B solder 10xAWG26 PUR 2.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/33481616A21020">https://b2b.harting.com/33481616A21020</a>

### Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type B
Connector 2	HARTING ix Industrial® Type B
Type of cable	Copper cable (round)

### Version

Cable length	2 m
Number of cores	10
Core structure	10x AWG 26
Termination method	Solder termination
Coding	Type B

### Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Limiting temperature	-40 ... +80 °C

### Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance  
Since 1945

Material properties

Colour (cable)	Grey
----------------	------

Specifications and approvals

Specifications	IEC 61076-3-124
----------------	-----------------

Commercial data

Packaging size	1
Net weight	127 g
Country of origin	Vietnam
European customs tariff number	85444290
GTIN	5713140260337
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33481616A21020](#)