

## Han F+B 17D PFT 0,5mm<sup>2</sup> f/- st/- PVC 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 440 0339 010
Specification	Han F+B 17D PFT 0,5mm <sup>2</sup> f/- st/- PVC 1,0m
HARTING eCatalogue	<a href="https://b2b.harting.com/33504400339010">https://b2b.harting.com/33504400339010</a>

### Identification

Category	System cabling
Series	Han <sup>®</sup> F+B
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Female Bulkhead mounted housing
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	17
Core structure	0.5 mm <sup>2</sup>
Number of contacts	17
PE contact	Yes

### Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-5 ... +70 °C moved -30 ... +80 °C unmoved
Minimum bending radius	4x Cable diameter (singular bending)



Pushing Performance  
Since 1945

Material properties

Material (cable)	PVC
Colour (cable)	Black Green-yellow

Specifications and approvals

Specifications	EN 50525-2-31
	IEC 60227-3
	IEC 60228
	EN 50363-3
	IEC 60227-3
	IEC 60332-1-2 Flame retardancy

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140238244
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33504400339010](#)