



Pushing Performance  
Since 1945

# HIGH STR. FO CABLE-MM-2CH.-10M,RING




Image is for illustration purposes only. Please refer to product description.

Part number	33 58 751 0100 001
Specification	HIGH STR. FO CABLE-MM-2CH.-10M,RING
HARTING eCatalogue	<a href="https://b2b.harting.com/33587510100001">https://b2b.harting.com/33587510100001</a>

## Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	FO cable
Description of the cable	Multimode

## Version

Cable length	10 m
Core structure	62.5 / 125 µm

## Technical characteristics

Cable diameter	7 mm
----------------	------

## Material properties

Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance  
Since 1945

Commercial data

Packaging size	1
Net weight	500 g
Net weight	36 g/m
Country of origin	Germany
European customs tariff number	85447000
GTIN	5713140273894
ETIM	EC000034
eCl@ss	27061803 Fiber optic cable

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33587510100001](#)