



Pushing Performance
Since 1945

7/8" m 4p screw 6-8mm str



Image is for illustration purposes only. Please refer to product description.

Part number	61 02 201 0211 00
Specification	7/8" m 4p screw 6-8mm str
HARTING eCatalogue	https://b2b.harting.com/6102201021100

Identification

Category	Connectors
Series	Circular connectors 7/8"
Element	Cable connector
Specification	Straight

Version

Gender	Male
Number of contacts	4
Locking type	Screw locking

Technical characteristics

Conductor cross-section	1.5 mm ²
Rated current	9 A
Rated voltage	300 V
Rated impulse voltage	4 kV
Pollution degree	3
Overvoltage category	III (protection by low voltage)
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-25 ... +85 °C
Cable diameter	6 ... 8 mm
Isolation group	I (600 ≤ CTI)



Pushing Performance
Since 1945

Material properties

Material (insert)	Polyamide (PA) Thermoplastic polyurethane (TPU)
Material (hood/housing)	Polybutylene terephthalate (PBT)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead Imidazolidine-2-thione
ECHA SCIP number	dd830bf5-8415-40c6-9706-42c221258c0b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140224629
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[6102201021100](#)