

ICC20_H_BS_ST_CG_13-17_EMC



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 1515
Specification	ICC20_H_BS_ST_CG_13-17_EMC
HARTING eCatalogue	https://harting.com/97000001515

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight EMC version

Version

Size	20
Version	Top entry

Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	13 ... 17 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE



Pushing Performance
Since 1945

Material properties

Colour (seal)	Blue
---------------	------

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[97000001515](#)