

5





4

3

2

1

harnessing dimensions



crimping tool of outer conductor:
hand tool: 09 99 000 0503 00
die: 09 99 000 0508 00 cavity B
with cables: RG179BU, RG187AU

crimping tool of inner conductor:
hand tool: 09 99 000 0501 00
die: 09 99 000 0507 00
with cables: AWG24, AWG26, AWG28, AWG30

A

								Det.	Name		Female coaxial contact 75 Ohms straight cable terminaison, inner and outer conductor for crimp termination	Maßstab/ Scale 5:1	
							Detail.	21-JUN-02	CV				
09691827230	Mating area	0,2 µm Au	0,2 µm Au				Insp.						All Dim. in mm
	Termination area	5 µm Sn	0,2 µm Au				Stand.						Orig. Size DIN A 4
09691825230	Mating area	0,8 µm Au	1,3 µm Au				HARTING EURL F-95972 Paris					TB 09 69 182 x230	Blatt/ Page 1 / 1
	Termination area	0,2 µm Au	1,3 µm Au	31057	21-JUN-02	CV							
Part number	Plating	outer conductor	inner conductor	Mod.	Det.	Name						Sub.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09691825230](#) [09691827230](#)