

SEK 40 Poles Female
CLOSED END COVER

SEK 40 Poles Female
CLOSED END COVER

CLOSED END COVER

CLOSED END COVER

NOTES:

1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.

2.) WHITE LABEL CONTENT:

CMK/YR-XXXXX-X-XX
HARTING P/N



HARTING P/N

BLACK FONT; FONT HEIGHT: 3.5.

- 3.) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).
- 4.) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

4.) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

Part-No.	Length-L
33 18 243 150 0069	1500mm
33 18 243 100 0057	1000mm
33 18 243 050 0055	500mm

			All Dimensions in mm Original Size DIN A 3		
Techn. Character.					
		Dat.		Name	
		Detail.		Andrew	
		Insp.			
		Stand.			
ZHUHAI HARTING LIMITED					
				Scale	
				/	
Free size tolerances					
SEK 40P FEMALE DOUBLE END FLAT TWIST CABLE ASSY,L=xM					
TB 33 18 0002 .00					
Sub.					
Page					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33182430500055](#) [33182431000057](#) [33182431500069](#)