

TOLERANCE FOR "L" LENGTH

Part-No.	Length-L
33 18 243 150 0068	1500mm
33 18 243 100 0062	1000mm
33 18 243 050 0060	500mm



NOTES:

- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
2.) WHITE LABEL CONTENT:

CWK/YR-XXXXXX-X-XX
HARTING P/N

BLACK FONT; FONT HEIGHT: 3.5.

- 3.) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION),
- 4.) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
			Det.	None	Scale		SEK 20P FEMALE DOUBLE END FLAT TWISTED PAIR CABLE ASSY,L=XM				
		Detail	11.08.08	Andrew.H	/						
		Insp.									
		Stand									
ZHUHAI HARTING LIMITED								TB 33 18 0003 .00			
Mod.	Da.t.	Name				Sub.			Page /		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33182430500060](#) [33182431000062](#) [33182431500068](#)