



Hybrid Han 3A - LC duplex and Power AC, with metal housing

X (2:1)

(without FO protection cap)

Loading-Plan
(Power DC version)

Shield (not connected)

- A — Orange
- B — Blue
- 1 — Black
- 2 — Blue
- PE — Green-Yellow

-Insertion loss must be tested 100%
-Return loss must be tested at least
by random samples

9	33571113005002	Hybrid cable 2xFO - 3x2.5/3.5		300
8	33571111005002			100
7	33571110605002			60
6	33571110505002			50
5	33571110405002			40
4	33571110205002			20
3	33571110105002			10
2	33571110055002			5
1	33571110015002			1
Cont No.	Part-No.	Type of cable		Dim.a
All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.	Ref. Sub.
All rights reserved Department EC PD - RO		Created by POPESCU	Inspected by AVRAM	Standardisation HOFFMANN
Title Han 3A FO Hybrid Cable Assembly		Date 2015-12-18	State Final Release	
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 3357111XXX5002	Rev. B
				Page 1/1

- Protection level: IP65/IP67
- Temperature range: -40°C ... +70°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33571113005002](#)