

D					
	Wire _____ Cu silver plated Gauge solid wire _____ AWG 30 / 1 (diameter : 0,25 mm) Voltage rating _____ 150 V Inductance _____ 0,39 μH/m (single end) _____ 0,56 μH/m (differential) Capacitance _____ 48,2 pF/m (single end) _____ 32,8 pF/m (differential) Impedance _____ 90 Ω (single end) _____ 130 Ω (differential) Signal delay _____ 4,10 ns/m Insulation material _____ FEP Temperature rating _____ -55°C to +150°C				
C					
B					
A					

				Dat.	Name		Flat cable Length per reel : 30,48 m 68 poles, UL 20726	Maßstab/ Scale 6:1
			Detail.	30/05/07	PK			
			Insp.					
			Stand.					
			HARTING EURL F-95972 Paris				TB 60 90 068 6007	Blatt/ Page 1 / 1
	34362	30/05/07	PK					
	Mod.	Dat.	Name				Sub.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[60900686007](#)