



- Loading-Plan:
- | | | |
|---|-------|---|
| 1 | brown | 1 |
| 2 | white | 2 |
| 3 | blue | 3 |
| 4 | black | 4 |



4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

Part no.	213496974XXXXX
----------	----------------

Type of cable	XX
PVC grey, 4x1.5mm ²	XX=95
PUR black, 4x1.5mm ²	XX=96

- Protection level: IP67
- Temperature range: -25°C ... +80°C

	All rights reserved Department EC PD - RO	All Dimensions in mm Original Size DIN A3		Scale 1.5:1	Free size tol.		Ref. Sub.	
		Created by TAMAS	Inspected by AVRAM	Standardisation HOFFMANN	Date 2014-07-01	State Final Release		
HARTING Electronics GmbH D-32339 Espelkamp		Title 7/8 Cable Assembly				Doc-Key / ECM-Nr. 100581015/UGD/009/A 500000076597		
		Type TB	Number 213496974XXXXX		Rev. A	Page 1/1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21349697496003](#) [21349697495003](#)