



Connector Location A

Connector Location B





X
male
(without protection cap)



Loading-Plan
(Power AC version)
(Shield not connected)


A	Orange	B
B	Blue	A
L1	Black	L1
N	Blue	N
PE	Green-Yellow	PE


Y
male
(without protection cap)



	All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved		Created by	Inspected by	Standardisation	Date	State	
	Department HCS - RO		COSTEA	COSTEA	POPESCUD	2017-09-05	Final Release	
	HARTING Customised Solutions		Title Han 3A FO Hybrid Cable Assembly				Doc-Key / ECM-Nr. 100183341/UGD/029/D 500000124744	
D-32427 Minden		Type	Number		Rev.		Page	
		TB	335721XXXX5001		D		1/2	


1		2		3		4		5		6		7		8	
A	38	33572111005001		Hybrid cable 2xFO MM 50/125 + 3x2.5mm², PVC, black		100		40	33572113005001		Hybrid cable 2xFO MM 50/125 + 3x2.5mm², PVC, black		300		
	37	33572110605001				60		39	33572112005001		200				
	36	33572110565001				56		Cont No.		Part-No.		Type of cable		Dim. a (m)	
	35	33572110505001				50									
	34	33572110465001				46									
B	33	33572110425001				42									
	32	33572110405001				40									
	31	33572110395001				39									
	30	33572110375001				37									
	29	33572110355001				35									
C	28	33572110345001				34									
	27	33572110325001				32									
	26	33572110305001				30									
	25	33572110285001				28									
	24	33572110265001				26									
D	23	33572110255001				25									
	22	33572110245001				24									
	21	33572110225001				22									
	20	33572110205001				20									
	19	33572110195001				19									
E	18	33572110185001				18									
	17	33572110175001				17									
	16	33572110165001				16									
	15	33572110155001				15									
	14	33572110145001				14									
F	13	33572110135001				13									
	12	33572110125001				12									
	11	33572110115001				11									
	10	33572110105001				10									
	9	33572110095001				9									
	8	33572110085001				8									
	7	33572120755001				7.5									
	6	33572110055001				5									
	5	33572120355001				3.5									
	4	33572120255001				2.5									
	3	33572110025001				2									
	2	33572120155001				1.5									
	1	33572110015001				1									
	Cont No.		Part-No.		Type of cable		Dim. a (m)								
	1		2		3		4		5		6		7		8

		All rights reserved		Created by COSTEA		Inspected by COSTEA		Standardisation POPESCU		Date 2017-09-05		State Final Release	
HARTING Customised Solutions D-32427 Minden				Title Han 3A FO Hybrid Cable Assembly				Doc-Key / ECM-Nr. 100183341/UGD/029/D 500000124744					
				Type TB		Number 335721XXXX5001				Rev. D		Page 2/2	



All rights reserved

Department HCS - RO



All Dimensions in mm

Tech. Character.

Free size tol.

Created by
COSTEA

Inspected by
COSTEA

Standardisation
POPESCU

Date
2017-09-05

State
Final Release

Title
Han 3A FO Hybrid Cable Assembly

Type
TB

Number
335721XXXX5001

Rev.
D

Page
2/2

Doc-Key / ECM-Nr.
100183341/UGD/029/D
500000124744

HARTING Customised Solutions

D-32427 Minden

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33572112005001](#) [33572110605001](#) [33572113005001](#)