



Connector Location A

Connector Location B





X
male
(without protection cap)

Y
male
(without protection cap)



Loading-Plan
 (Power DC version)
 (Shield not connected)

A	Orange	B
B	Blue	A
1	Black	1
2	Blue	2
PE	Green-Yellow	PE



10	33572113005002	Hybrid cable 2xFO MM 50/125 + 3x2.5mm ² , PVC, black	300
9	33572112005002		200
8	33572111005002		100
7	33572110605002		60
6	33572110505002		50
5	33572110405002		40
4	33572110205002		20
3	33572110105002		10
2	33572110055002		5
1	33572110015002		1

Cont no.	Part-no.	Type of cable	Dim. a (m)
----------	----------	---------------	------------



All Dimensions
in mm

	Tech. Character.
--	------------------

Free size tol.

According to production drawing



All rights reserved

Department HCS - R0

Created by
COSTEA

Inspected by COSTEA	
------------------------	--

Standardisation
POPESCUD

Date	2017-09-04
------	------------

State
Final Release

Title	Han 3A FO Hybrid Cable Assembly
-------	---------------------------------

Type TB

Number	3357211XXX5002
--------	----------------

Doc-Key / ECM-Nr.
100183341/UGD/033/B
500000124745

Rev. **B**Page
1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33572110605002](#) [33572113005002](#)