











Stromlaufplan /
Schematic diagram

1		Litze braun (+) / flexible conductor brown (+)		1
2		Litze weiss (Ö) / flexible conductor white (O)		2
4		Litze schwarz (S) / flexible conductor black (S)		4
3		Litze blau (-) / flexible conductor blue (-)		3

Halogen-freie PUR-Leitung 4x0,34mm²
in schwarz mit UL/CSA-Zulassung /
Halogen-free PUR-conductor 4x0,34mm²
black with approval according to UL/CSA

21 03 415 5401	0,3m
21 03 415 5402	0,6m
21 03 415 5403	1,0m
21 03 415 5404	1,5m
21 03 415 5405	2,0m
Artikelnr.	Nennlänge (L)



 All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse / Free size tolerances	
				Dat.	Name	Massstab / Scale 1:1	M12-Rundsteckverbinder Buchse gewinkelt Stift gerade / <i>M12-circular connector</i> <i>female angular male straight</i>
			Detail.	22.11.04	Ho		
			Insp.		WELL		
			Stand.				
411416	17.01.05	Ho	HARTING Electric GmbH & Co. KG			TB 21 03 415 5400	Blatt / page
411399	10.01.05	Ho	D-32339 Espelkamp				
411338							
Mod.	Dat.	Name				Sub.	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21034155401](#) [21034155402](#)