


A


B

C

D




Stromlaufplan /
Schematic diagram





1	—	Litze braun (+) / flexible conductor brown (+)
2	—	Litze weiss (Ö) / flexible conductor white (O)
4	—	Litze schwarz (S) / flexible conductor black (S)
3	—	Litze blau (-) / flexible conductor blue (-)

Halogen-freie PUR-Leitung 4x0,34mm²
in schwarz mit UL/CSA-Zulassung /
Halogen-free PUR-conductor 4x0,34mm²
black with approval according to UL/CSA

21 03 515 4401	1,5m
21 03 515 4402	3,0m
21 03 515 4403	5,0m
21 03 515 4404	7,5m
21 03 515 4405	10,0m
Artikelnr.	Nennlänge (L)



 All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse! Free size tolerances	
				Dat.	Name	Massstab/Scale 1:1	M12-Rundsteckverbinder Buchse gewinkelt / M12-circular connector female angular
			Detail.	22.11.04	Ho		
			Insp.		WELL		
			Stand.				
411416	17.01.05	Ho	HARTING Electric GmbH & Co. KG D-32339 Espelkamp				TB 21 03 515 4400
411399	10.01.05	Ho					
411338							
Mod.	Dat.	Name				Sub.	Blatt/ page

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21035154402](#) [21035154405](#)