






Dichtungseinsatz/sealing insert	
mit Inlet/with Inlet	ohne Inlet/without Inlet
min. $\phi 15$, max. $\phi 20$	min. $\phi 20$, max. $\phi 25$



			All Dimensions in mm Original Size DIN A 4				Techn. Character.			Nicht tolerierte Masse/ Free size tolerances		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005152](#)