






PRODUCT NO.
10116657-x52xx






RECOMMENDED MOUNTING P.C.B LAYOUT




PRODUCT NO.

10116657-x52xx



RECOMMENDED MODULE P.C.B LAYOUT



Copyright FCI.
FCI



DDR SO-DIMM 0.6mm PITCH 200 POS
REVERSE TYPE ASS'Y
catalog no

dag no

10116657

Rev.
A

CUSTOMER COPY sheet 3 of 4

PDM: Rev:A

STATUS Released

Printed: Apr 22, 2011

1		2		3		4		5		6		7		8	
PRODUCT NO.		LOCATING PEG		TERMINAL CONTACT AREA FINISH		HOLD DOWN FINISH		SOLDER TAIL FINISH							
A	10116657-052FS	YES		Au FLASH		Pure Sn PLATING		Au FLASH PLATING		10116657- LF For Rohs OPTIONS: TAIL PLATING CODE MUST BE 0~3. HOLD DOWN PLATING CODE MUST BE "S". "LF" CODE IS EXIST IN THE END. EX: 10116657-252TSLF FOR NOT Rohs COMPATIBLE: THIS "LF" CODE IS "BLANK". EX:10116657-452TS <PACKING METHOD> R : TAPE REEL DEFAULT : TRAY <HOLD DOWN FINISH> S : Pure Sn B : Sn-Pb <CONTACT AREA FINISH> F : Au FLASH T : Au 0.3μm MIN. A : Au 0.76μm MIN. <TOTAL HEIGHT> 52 : 5.2mm <LOCATING PEG, SOLDER TAIL FINISH> 0 : YES, Au FLASH 1 : NO, Au FLASH 2 : YES, Pure Sn PLATING 3 : NO, Pure Sn PLATING 4 : YES, Sn-Pb PLATING 5 : NO, Sn-Pb PLATING					
	10116657-152FS	NO													
	10116657-052TS	YES													
	10116657-152TS	NO													
	10116657-052AS	YES													
	10116657-152AS	NO													
B	10116657-052FC	YES		Au FLASH		Sn-Pb PLATING		Au FLASH PLATING							
	10116657-152FC	NO													
	10116657-052TC	YES													
	10116657-152TC	NO													
	10116657-052AC	YES													
	10116657-152AC	NO													
C	10116657-252FS	YES		Au FLASH		Pure Sn PLATING		Pure Sn PLATING							
	10116657-352FS	NO													
	10116657-252TS	YES													
	10116657-352TS	NO													
	10116657-252AS	YES													
	10116657-352AS	NO													
D	10116657-252FC	YES		Au FLASH		Sn-Pb PLATING		Pure Sn PLATING							
	10116657-352FC	NO													
	10116657-252TC	YES													
	10116657-352TC	NO													
	10116657-252AC	YES													
	10116657-352AC	NO													
E	10116657-452FS	YES		Au FLASH		Pure Sn PLATING		Sn-Pb PLATING							
	10116657-552FS	NO													
	10116657-452TS	YES													
	10116657-552TS	NO													
	10116657-452AS	YES													
	10116657-552AS	NO													
F	10116657-452FC	YES		Au FLASH		Sn-Pb PLATING		Sn-Pb PLATING							
	10116657-552FC	NO													
	10116657-452TC	YES													
	10116657-552TC	NO													
	10116657-452AC	YES													
	10116657-552AC	NO													

FCI

Copyright FCI.

FCI

DDR SO-DIMM 0.6mm PITCH 200 POS

REVERSE TYPE ASS'Y

catalog no

deg no

10116657

Rev.

A

CUSTOMER COPY

sheet 4 of 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10116657-052FC](#) [10116657-052FSLF](#) [10116657-452AC](#) [10116657-252ASLF](#) [10116657-052ASLF](#) [10116657-052TSLF](#) [10116657-152FSLF](#)