






PRODUCT NO.
10117867-x52xx



RECOMMENDED MOUNTING P.C.B LAYOUT



Copyright FCI.
FCI

FCI	DDR SO-DIMM 0.6mm PITCH 200 POS		Rev.
	STANDARD TYPE ASS'Y		A
	catalog no		
10117867C		CUSTOMER COPY	sheet 3 of 4

1		2		3		4		5		6		7		8	
PRODUCT NO.		LOCATING PEG	TERMINAL CONTACT AREA FINISH	HOLD DOWN FINISH		SOLDER TAIL FINISH									
A	10117867-052FS	YES	Au FLASH	Pure Sn PLATING	Au FLASH PLATING										
	10117867-152FS	NO													
	10117867-052TS	YES	Au 0.3μm MIN.												
	10117867-152TS	NO													
	10117867-052AS	YES	Au 0.76μm MIN.												
	10117867-152AS	NO													
B	10117867-052FC	YES	Au FLASH	Sn-Cu PLATING	Au FLASH PLATING										
	10117867-152FC	NO													
	10117867-052TC	YES	Au 0.3μm MIN.												
	10117867-152TC	NO													
	10117867-052AC	YES	Au 0.76μm MIN.												
	10117867-152AC	NO													
C	10117867-252FS	YES	Au FLASH	Pure Sn PLATING	Pure Sn PLATING										
	10117867-352FS	NO													
	10117867-252TS	YES	Au 0.3μm MIN.												
	10117867-352TS	NO													
	10117867-252AS	YES	Au 0.76μm MIN.												
	10117867-352AS	NO													
D	10117867-252FC	YES	Au FLASH	Sn-Cu PLATING	Pure Sn PLATING										
	10117867-352FC	NO													
	10117867-252TC	YES	Au 0.3μm MIN.												
	10117867-352TC	NO													
	10117867-252AC	YES	Au 0.76μm MIN.												
	10117867-352AC	NO													
E	10117867-452FS	YES	Au FLASH	Pure Sn PLATING	Sn-Pb PLATING										
	10117867-552FS	NO													
	10117867-452TS	YES	Au 0.3μm MIN.												
	10117867-552TS	NO													
	10117867-452AS	YES	Au 0.76μm MIN.												
	10117867-552AS	NO													
F	10117867-452FC	YES	Au FLASH	Sn-Cu PLATING	Sn-Pb PLATING										
	10117867-552FC	NO													
	10117867-452TC	YES	Au 0.3μm MIN.												
	10117867-552TC	NO													
	10117867-452AC	YES	Au 0.76μm MIN.												
	10117867-552AC	NO													

10117867-

LF

For Rohs OPTIONS:
TAIL PLATING CODE MUST BE 0~3.
HOLD DOWN PLATING CODE MUST BE "S".
"LF" CODE IS EXIST IN THE END.
EX: 10117867-252TSLF

FOR NOT Rohs COMPATIBLE:
THIS "LF" CODE IS "BLANK".
EX:10117867-452TS

<PACKING METHOD>
R : TAPE REEL
DEFAULT : TRAY

<HOLD DOWN FINISH>
S : Pure Sn
B : Sn-Pb

<CONTACT AREA FINISH>
F : Au FLASH
T : Au 0.3μm MIN.
A : Au 0.76μm MIN.

<TOTAL HEIGHT>
52 : 5.2mm

<LOCATING PEG, SOLDER TAIL FINISH>
0 : YES, Au FLASH
1 : NO, Au FLASH
2 : YES, Pure Sn PLATING
3 : NO, Pure Sn PLATING
4 : YES, Sn-Pb PLATING
5 : NO, Sn-Pb PLATING

FCI

Copyright FCI.

REV. F - 2006-04-17

FCI

DDR SO-DIMM 0.6mm PITCH 200 POS

STANDARD TYPE ASS'Y

catalog no

diag. no

CUSTOMER COPY

sheet 4 of 4

Rev.

10117867C

A

1

2

3

4

5

6

7

8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10117867-052FC](#) [10117867-052FSLF](#) [10117867-052TSLF](#) [10117867-052ASLF](#) [10117867-152FSLF](#) [10117867-152TSLF](#) [10117867-252TSLF](#)