






PRODUCT NUMBER

10141569-0001LF


RECOMMENDED P.C.B LAYOUT
ALL TOLERANCE ARE: ±0.05

NOTE:

1. CURRENT RATING: 3A AC/DC.
2. WITHSTANDING VOLTAGE: 600V AC/MINUTE.
3. TEMPERATURE RANGE: -40~125°C.
4. INSULATION RESISTANCE: ≥5000MΩ.
5. CONTACT RESISTANCE: ≤20mΩ.
6. PLASTIC MATERIAL: PA6T, UL94V-0, BLACK.
7. TERMINAL MATERIAL: PHOSPHOR BRONZE.
8. FINISH: GOLD FLASH.




Plating Zone Reference




Section A-A

mat'l. code				surface	tolerance	projection	product family			
litr	ecr no	dr	date	tolerances unless otherwise specified			MINITEK			
B	ELX-N-30190	TONY	2018-05-16	angles	linear		title			
					16<L ≤ ±0.40	mm	2.54mm RECEPTACLE			
					4<L ≤ ±0.30		VERTICAL, 30 POS.			
				0°±5°	L ≤ 4 ±0.20	scale N.T.S.	dwg no			
				dr	TONY LENG	2017-12-12	sheet 1 of 2			
				enrg	TONY LENG	2017-12-12	10141569			
				chr	ZK_HU	2017-12-12	A4			
				appd	TIM_YAO	2017-12-12	type			
sheet index	revision	B	B				Product Customer Drawing			
	sheet	1	2							




NOTES:

1. Reel[$\varnothing 330 \times 77\text{mm}$]
2. 300pcs/R, 4R/Carton, 1200pcs/Carton
3. Heat-sealing cover tape
4. Black carrier
5. Big Plastic Bag(1000*1000mm)
6. Carton(340*340*325mm, Thickness=5mm)
7. In each Big Plastic bag put two desiccants



CARRIER TAPE PACKING LENGTH



mat'l. code				surface	tolerance	projection	product family			
ltr	ecn no	dr	date	tolerances unless otherwise specified			MINITEK			
				angles	linear	mm	title			
					$16 \leq L \pm 0.40$		2.54mm RECEPTACLE			
					$4 < L \leq 16 \pm 0.30$		VERTICAL, 30 POS.			
				$0 \pm 5^\circ$	$L \leq 4 \pm 0.20$	scale N.T.S.				
		dr	TONY LENG	2017-12-12			dwg no		sheet 2 of 2	size
		engr	TONY LENG	2017-12-12			10141569			A4
		chr	ZK_HU	2017-12-12						
		appd	TIM_YAO	2017-12-12						
sheet index	revision	B	B				type Product Customer Drawing			
	sheet	1	2							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10141569-0001LF](#)