







REV.	DATE	DESCRIPTION
A	09/29/98	ADD X-SECTION OF BODY



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE
1 BODY	BRASS	NICKEL	DRAWN	G.R.S.	09/29/98
2 INSULATOR	TEFLON	NATURAL	CHECKED		
3 CONTACT PIN	PHOS. BRONZE	GOLD	ISSUED		
4 FERRULE	BRASS	NICKEL			
5 LOCK WASHER	BRASS	NICKEL			
6 HEX NUT	BRASS	NICKEL			
7					
8					

**Connex**  
Connector Corporation

TITLE: BNC REVERSE POLARIZED BULKHEAD CRIMP JACK  
FRONT MOUNT - 174, 188, 316 CABLE

SCALE: NA PART NO. 112587-RP SHEET 1 OF 1

SIZE: A DWG. NO. 99001 REV. A

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS FOR CUSTOMER REFERENCE ONLY

TOLERANCES FOR MILLIMETERS ARE:

0.3 - 0.6 ± 0.2  
0.6 - 1.2 ± 0.1  
1.2 - 3.0 ± 0.1  
3.0 - 6.0 ± 0.2  
6.0 - 15.0 ± 0.3  
15.0 - 30.0 ± 0.4  
30.0 - 100.0 ± 0.5  
100.0 - 200.0 ± 0.6  
200.0 - 500.0 ± 0.8  
500.0 - 1000.0 ± 1.0

DO NOT SCALE DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112587RP](#)