


REV. STATUS SHEETS	REV.LTR.	-	REVISIONS			
	SHEET NO	1	LTR	DESCRIPTION	DATE	BY
			-	Released	3/04/96	JCL



Materials & Finishes

Center Contact: Silver Plated Beryllium Copper
Other Metal Parts: Silver Plated Brass
Backnut: Silver Plated Brass
Dielectric: Teflon
Gaskets: Silicone Rubber
Attachment: Clamp

Electrical Properties

Impedance: 50 Ohms
Working Voltage: 2700 Volts (RMS max)
VSWR: 1.20:1 up to 2 GHz
Insertion Loss: <0.15 dB up to 2 GHz

Unless otherwise specified dimensions in inches. Tolerances are applicable when specified.	Approvals			TIMES MICROWAVE SYSTEMS Wallingford, CT 06492		
	Drawn	JCL	3/04/96	TC-400-716FC Type 7-16 DIN Female Connector for LMR-400		
	Check					
	PrjMg					
	PrdMg			Size A	Code Ident 68999	Dwg.No. 3190-376
	QAMgr			Scale: NA		Sheet: 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TC-400-716FC](#)