


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 52689	07/23	SEE PDM




MATERIAL:

SMP FEMALE CONNECTOR:	1222-4004
2.92MM MALE CONNECTOR:	SF1511-60069
FLEXIBLE .047 CABLE:	200-70-479
SINGLE WALL TUBING:	M23053/5 (BLACK)

TABLE I		
SV P/N	L (IN)	INSERTION LOSS dB MAX.
7012-1066	6.00	1.52
7012-1067	12.00	2.62

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 32 GHz
VSWR:	1.39:1, DC TO 32 GHz
INSERTION LOSS:	SEE TABLE

MATERIAL: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		
FINISH: SEE NOTES			TITLE: SMP FEMALE TO 2.92MM MALE FLEXIBLE .047 CABLE ASSEMBLY	
SURFACE AREA: N/A	THIRD ANGLE PROJECTION 	DRAWN: MAL 06/16/16 CHECKED: SEE PDM APPROVED: SEE PDM	SIZE B	DWG. NO. 7012-1066-1067
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.			SCALE: 3:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7012-1067](#)