


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
B	DCN 52753	07/23	SEE PDM



MATERIAL:

2 SMPM FEMALE CONNECTORS:	3221-40007
FLEXIBLE .047 CABLE:	200-70-479
SINGLE WALL TUBING:	M23053/5 (BLACK)

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 40.0 GHz
VSWR:	1.56:1 DC TO 40.0 GHz
INSERTION LOSS:	SEE TABLE

SV P/N	L (OAL)	INSERTION LOSS dB MAX.
7032-6351	6.000"	1.80
7032-6352	12.000"	3.21
7032-6353	24.000"	6.06

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		www.svmicrowave.com	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' 					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-6353](#)