


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
B	DCN 52740	07/23	SEE PDM





MATERIAL:

CONNECTORS:	SMPM JACK (3221-40007)
	SMA PLUG (SF2911-60172)
CABLE:	FLEXIBLE Ø.047 CABLE (200-70-479)
SHRINK TUBING:	M23053/5

SV P/N	OAL
7032-7524	6.000
7032-7525	12.000

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 18.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$ X°X' $\pm 15'$ DECIMAL: .X $\pm .030$.XX $\pm .010$.XXX $\pm .005$ INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		<div> www.svmicrowave.com</div>	
FINISH:	SEE NOTES						
SURFACE AREA:	N/A						
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		<div>THIRD ANGLE PROJECTION</div> <div></div>		DRAWN: SJ 04/01/19		TITLE: SMPM FEMALE TO SMA MALE FOR .047 FLEXIBLE CABLE ASSEMBLY	
<div>SIZE B DWG. NO. 7032-7524-7525</div>				CHECKED: SEE PDM			
				APPROVED: SEE PDM			
				SCALE: 1:2		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-7524](#)