


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 46867	07/22	SEE PDM



MATERIAL:



CONNECTORS: SMPM FEMALE R/A (3222-40080)
SMPM FEMALE (3221-40128)

CABLE: .047 SUPERFLEX CABLE

PERFORMANCE:

IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 33.0 GHz

SV P/N	OAL
7032-9433	3.000
7032-9434	6.000

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		<div>www.svmicrowave.com</div> <div>TITLE: SMPM FEMALE R/A TO SMPM FEMALE CABLE ASSEMBLY FOR .047 SUPERFLEX CABLE</div>	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS			
SURFACE AREA: N/A		DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005				SIZE DWG. NO. 7032-9433-9434	
PROPRIETARY		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		THIRD ANGLE PROJECTION		DRAWN: SJ 07/20/22	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: SEE PDM		SCALE: 6:1	
				APPROVED: SEE PDM		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-9433](#)