





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8AP-02AFFM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * QC Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Cable: UL2464 22AWG*2C+Talcum, PVC Jacket, UV Resistant, OD=4.2, Black.
 - * Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02~05M: $\pm 60\text{mm}$
06~10M: $\pm 100\text{mm}$
11~30M: $\pm 200\text{mm}$
31~99M: $\pm 500\text{mm}$



Pin Assignments
Front View



2	Red 紅
1	Black 黑
Conn.	Wire Color
Pin Out	

UNIT:mm		TITLE M8 2Pin Cable F Conn. F Pin
TOLERANCE $\pm 0.5 \text{ mm}$	SCALE 2:1	SIZE A4
	REV. A	SHEET 1 OF 1
	WC-REV. A.4	QC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2014-01-09
DWG NO 8AP-02AFFM-SL7AXX	CHECKED BY Jimmy	DATE 2014-01-09
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-02AFFM-SL7A03](#) [8AP-02AFFM-SL7A05](#) [8AP-02AFFM-SL7A10](#)