



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8AP-02AMMM-SL7AXX


XX: 01~99Meters
01: 01Meter
02: 02Meter
...

99: 99Meters

Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: PU, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Nylon+GF, Black.
- * Cable: UL2464 22AWG*2C+Talcum, PVC Jacket, UV Resistant, OD=4.2, Black.
- * Cable Length Tolerance:
 - 01M: ± 40 mm
 - 02~05M: ± 60 mm
 - 06~10M: ± 100 mm
 - 11~30M: ± 200 mm
 - 31~99M: ± 500 mm



Pin Assignments
Front View

2	Red 紅
1	Black 黑
Conn.	Wire Color
Pin Out	

UNIT:mm		TITLE
TOLERANCE ± 0.5 mm		
M8 2Pin Cable M Conn. M Pin		
SCALE	SIZE	SHEET
2:1	A4	1 OF 1
REV.	WC-REV.	QC: Inspection item
A	A.3	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
8AP-02AMMM-SL7AXX	Mila	2014-01-09
CUSTOMER	CHECKED BY	DATE
ALTW	Jimmy	2014-01-09
	APPROVED BY	DATE
	Jerry	2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-02AMMM-SL7A02](#) [8AP-02AMMM-SL7A03](#) [8AP-02AMMM-SL7A05](#) [8AP-02AMMM-SL7A10](#)