




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION




Conn.



8AP-04AFFM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Cable: UL2464 22AWG*4C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
 - * Cable Length Tolerance: 01M: ± 40 mm
02~05M: ± 60 mm
06~10M: ± 100 mm
11~30M: ± 200 mm
31~99M: ± 500 mm



Pin Assignments
Front View



4	Black 黑
3	Blue 藍
2	White 白
1	Brown 棕
Conn.	Wire Color

Pin Out

UNIT:mm		TITLE
TOLERANCE	± 0.5 mm	M8 4Pin Cable F Conn. F Pin
SCALE	2:1	SIZE A4
REV.	A	SHEET 1 OF 1
WC-REV.	A.4	$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Mila	2014-01-09
CUSTOMER	CHECKED BY	DATE
ALTW	Jimmy	2014-01-09
	APPROVED BY	DATE
	Jerry	2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-04AFFM-SL7A02](#) [8AP-04AFFM-SL7A03](#) [8AP-04AFFM-SL7A05](#) [8AP-04AFFM-SL7A10](#)