



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Cable ②

8AP-04AMMM-SL7000 ①
Color: Black

Conn.



8AP-04AMMM-SL7AXX


XX: 01~99Meters
01: 01Meter
02: 02Meter
...

99: 99Meters

Cable Length(L): 01~99Meters

Note:


- * ① Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: PU, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Nylon+GF, Black.
- * Cable: UL2464 22AWG*4C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
- * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



Pin Assignments
Front View

4	Black 黑
3	Blue 藍
2	White 白
1	Brown 棕
Conn.	Wire Color
Pin Out	

UNIT:mm



TOLERANCE
±0.5 mm

TITLE M8 4Pin Cable M Conn. M Pin			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.2	① Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2014-01-09
DWG NO 8AP-04AMMM-SL7AXX	CHECKED BY Jimmy	DATE 2014-01-09
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-04AMMM-SL7A02](#) [8AP-04AMMM-SL7A03](#) [8AP-04AMMM-SL7A05](#) [8AP-04AMMM-SL7A10](#)