



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8AP-05AFFM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters



Note:
* (QC) Important Dimension.
* Waterproof Rate: IP67.
* Connector: PU, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Screw Nut: Nylon+GF, Black.
* Cable: UL2464 24AWG*5C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



Pin Assignments
Front View

5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

Pin Out

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	M8 5Pin Cable F Conn. F Pin
SCALE	2:1	SIZE A4
REV.	A	WC-REV. A.3
		(QC): Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Mila	2014-01-09
CUSTOMER	CHECKED BY	DATE
ALTW	Jimmy	2014-01-09
	APPROVED BY	DATE
	Jerry	2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-05AFFM-SL7A03](#) [8AP-05AFFM-SL7A05](#) [8AP-05AFFM-SL7A10](#)