






REV.	ECN NO.	DATE	SIGN	DESCRIPTION



XX: 01~99Meters
01: 01Meter
02: 02Meter
...

99: 99Meters
Cable Length(L): 01~99Meters



Pin Assignments
Front View

5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

Pin Out

UNIT:mm
TOLERANCE
±0.5 mm

TITLE M8 5Pin Cable M Conn. M Pin			
SCALE 9:5	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.2	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2014-01-09
DWG NO 8AP-05AMMM-SR7AXX	CHECKED BY Jimmy	DATE 2014-01-09
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-01-09

Note:
* $\varnothing$ Important Dimension.
* Waterproof Rate: IP67.
* Connector: PU, Black.
* Male Pin: Copper Alloy, Gold Plated.
* Screw Nut: Nylon+GF, Black.
* Cable: UL2464 24AWG*5C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-05AMMM-SR7A02](#) [8AP-05AMMM-SR7A03](#) [8AP-05AMMM-SR7A05](#) [8AP-05AMMM-SR7A10](#)