



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION






Conn.

Cable ② 8H-05AFFM-SL7000
Color: Black

①

8H-05AFFM-SL7AXX

XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters



Pin Assignments
Front View

5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

Note:
* Ⓞ Important Dimension.
* Waterproof Rate: IP67.
* Connector: PU, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Screw Nut: Zinc Alloy, Nickel Plated.
* O-Ring: Viton, Green.
* Cable: UL2464 24AWG*5C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

UNIT:mm		TITLE M8 5Pin Cable F Conn. F Pin	
TOLERANCE ±0.5 mm		SCALE 2:1	SIZE A4
REV. A	WC-REV. A.1	SHEET 1	OF 1
Ⓞ: Inspection item			

ITEM NO		DRAWN BY Mila	DATE 2014-01-09
DWG NO 8H-05AFFM-SL7AXX		CHECKED BY Jimmy	DATE 2014-01-09
CUSTOMER ALTW		APPROVED BY Jerry	DATE 2014-01-09

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8H-05AFFM-SL7A02](#) [8H-05AFFM-SL7A03](#) [8H-05AFFM-SL7A05](#) [8H-05AFFM-SL7A10](#)