


RECOMMENDED PCB LAYOUT



DIMENSION

A	(N-1)×3.5+4.90
B	(N-1)×3.5

N= NUMBER OF CONCATS

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'05	Dim changed from 3.8 to 3.5	Marvin
△	04/20'06	Added feature	Marvin
△	8/16'06	Added VDE standard	Steady
△	1/11'07	Soldering temperature changed from 245° to 250°	Tony
△	5/27'08	Operating temperature is changed	Marvin
△	3/17'09	The dimensions is changed from 2.3mm to 2.5mm	Jacke
△	2009.08.18	The material is changed	Jacke
△	2011.03.16	The dimensions is changed from 2.5mm to 2.45mm	Aaron
△	2012.05.14	Voltage rating is changed	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- ⑦ ● Item ② Male contact pin: Copper Tin plated
- Item ③ Terminalhousing: Thermoplastic (UL94V-0)

- ③ Electrical: cULus /VDE
- ③ ● Voltage rating: 300V/300V
- Current rating: 10A/10.5A
- Withstanding Voltage: 1.6 KV/2.5KV
- ⑤ ● Operating temperature: -40°C to +115°C
- ④ ● Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus VDE
- Critical dimension: △

OQ xx 1 2 x 1 xxxx G

No. OF POLES
02: 2 POLES

24: 24 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "Q" Logo
000A: "ANYTEK" Logo
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OQ 3.5mm Series 90° (2P-24P) Triangle Key Lock					
PART NO.	OQxx12x1xxxxG			DWG NO.	80Q0402	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Chen Bo 05/14'12	Chen Bo 05/14'12		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
						X.XX ±0.10
						X° ±1°

SHEET: 01/01

REV.: L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[OQ0312510000G](#)