






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1670042~47	2016/07/05	Jinhai	Change Note
C	C190347	2019/03/06	Vicky	Change Note
D	C211805	2021/12/07	Leon	 *1




Recommended Panel
Cut-Out




7 PIN
6 PIN
Pin Assignments Front View

ADC-XXPMMS-LS7001


02: 2Pin
07: 7Pin



5 PIN
4 PIN




3 PIN



2 PIN

Pin Assignments Front View



Note:

- *  Important Dimension To Check.
- * Waterproof Rate: IPX7, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Gasket: Rubber, Gray.
- * Nut: Thermoplastic, Black.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 1.8mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm
- * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝，散裝出貨)

UNIT: mm		TITLE LARGE PANEL LOCK M CONN M PIN
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	SCALE 1:1	SIZE A4
	REV. D	SHEET 1 OF 1
	WC-REV. A.2	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY Vicky	DATE 2016-07-05
DWG NO. ADC-XXPMMS-LS7001	CHECKED BY Mafei	DATE 2016-07-05
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2016-07-05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ADC-07PMMS-LS7001](#) [ADC-05PMMS-LS7001](#) [ADC-02PMMS-LS7001](#) [ADC-06PMMS-LS7001](#) [ADC-03PMMS-LS7001](#) [ADC-04PMMS-LS7001](#)