


REV.	DATE	DESCRIPTION
NC	06/08/06	INITIAL RELEASE



NOTE:

- 1) TESTING VALUE VSWR 1.2 MAX. AT 0.3 MHZ~1 GHZ
- 2) RESISTOR 0.5% - 1 WATT

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	<div>Amphenol Connex</div> <div>BNC TERMINATOR PLUG W/ CHAIN (50 ohms)</div> <div>PART NO. 202113-10</div>							
8					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.		06/08/06						
7					0.5 – 8mm ± 0.20mm	CHECKED									
6					8 – 30mm ± 0.40mm	ISSUED									
5					30 – 120mm ± 0.50mm										
4					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	SHEET	1 OF 1								
3	CONTACT PIN	BRASS	GOLD	1	.020 – .315 = ± 0.007"										
2	INSULATOR	TEFLON	NATURAL	1	.315 – 1.180 = ± 0.015"										
1	BODY	BRASS	NICKEL	1	1.180 – 4.724 = ± 0.020"										
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/202/202113-10.DWG		DWG. NO.	202113-10.DWG	REV.	NC	SIZE	A	SCALE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[202113-10](#)