


TV07R (D38999/24) – Crimp, Metal CTV07R (D38999/24) – Crimp, Composite

Jam Nut Receptacle

PART

To complete,
see how to order
pages 25-27.

Connector Type	Shell Style	Service Class	Shell Size & Insert Arrg	Contact Type	Alternate Position	Special Variations
TV	07	RW	9-35	P	B	(453)
TVS	07	RK	X-X	X	X	(XXX)
TVS	07	RF	X-X	X	X	(XXX)
TVS	07	RS	X-X	X	X	(XXX)
CTV	07	RW	X-X	X	X	(XXX)
CTVS	07	RF	X-X	X	X	(XXX)
D38999/	24	X	X-X	X	X	NA



† Red band indicates fully mated

†† Blue band indicates rear release contact retention system

★ .059 dia min.

1.5 dia min., 3 lockwire holes Formed lockwire hole design (6 holes) is optional Inches

Shell Size	MS Shell Size Code	B Thread Class 2A 0.1P-0.3L-TS (Plated)	C Max.	D ¹ +.010 - .000	D ² +.000 - .010	H Hex +.017 - .016	S ±.010
9	A	.6250	1.199	.693	.657	.875	1.062
11	B	.7500	1.386	.825	.770	1.000	1.250
13	C	.8750	1.511	1.010	.955	1.188	1.375
15	D	1.0000	1.636	1.135	1.085	1.312	1.500
17	E	1.1875	1.761	1.260	1.210	1.438	1.625
19	F	1.2500	1.949	1.385	1.335	1.562	1.812
21	G	1.3750	2.073	1.510	1.460	1.688	1.938
23	H	1.5000	2.199	1.635	1.585	1.812	2.062
25	J	1.6250	2.323	1.760	1.710	2.000	2.188

Millimeters

Shell Size	MS Shell Size Code	C Max.	D ¹ +.25 - .00	D ² +.00 - .25	H Hex +.43 - .41	S ±.25	V Thread Metric
9	A	30.45	17.60	16.70	22.23	26.97	M12X1-6g
11	B	35.20	20.96	19.59	25.40	31.75	M15X1-6g
13	C	38.38	25.65	24.26	30.18	34.93	M18X1-6g
15	D	41.55	28.83	27.56	33.32	38.10	M22X1-6g
17	E	44.73	32.01	30.73	36.53	41.28	M25X1-6g
19	F	49.50	35.18	33.91	39.67	46.02	M28X1-6g
21	G	52.65	38.35	37.08	42.80	49.23	M31X1-6g
23	H	55.85	41.53	40.26	46.02	52.37	M34X1-6g
25	J	59.00	44.70	43.43	50.80	55.58	M37X1-6g

All dimensions for reference only NOTE: Deep reach receptacles are available for panel thicknesses up to .750 max.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[D38999/24KG39SB](#) [D38999/24MB35PN](#) [D38999/24WE2PN](#) [D38999/24FJ11AE](#) [D38999/24FJ11BC](#)
[D38999/24FJ11BE](#) [D38999/24FJ11PE](#) [D38999/24FJ11SC](#) [D38999/24FJ11SE](#) [D38999/24FJ20AE](#)
[D38999/24FJ20BE](#) [D38999/24FJ20PE](#) [D38999/24FJ20SE](#) [D38999/24KJ11BB](#) [D38999/24KJ11SB](#)
[D38999/24KJ20AA](#) [D38999/24KJ20AB](#) [D38999/24KJ20AN](#) [D38999/24KJ20BA](#) [D38999/24KJ20BB](#)
[D38999/24KJ20BN](#) [D38999/24KJ20PA](#) [D38999/24KJ20PB](#) [D38999/24KJ20SA](#) [D38999/24KJ20SB](#)
[D38999/24SJ11BA](#) [D38999/24SJ11SA](#) [D38999/24SJ20AA](#) [D38999/24SJ20AN](#) [D38999/24SJ20BA](#)
[D38999/24SJ20BN](#) [D38999/24SJ20PA](#) [D38999/24SJ20SA](#) [D38999/24SJ20SN](#) [D38999/24WJ11AE](#)
[D38999/24WJ11BE](#) [D38999/24WJ11PE](#) [D38999/24WJ11SE](#) [D38999/24WJ20AE](#) [D38999/24WJ20BE](#)
[D38999/24WJ20PE](#) [D38999/24FG39PB](#) [D38999/24KG16PA](#) [D38999/24MC35AN](#) [D38999/24FH35BN](#) [TVS07RF-11-](#)
[35P](#) [TVS07RK-21-35P](#) [TVS07RF-21-35S](#) [TVS07RF-15-5P](#) [TVS07RK-21-75S](#) [TVS07RF-15-35P-LC](#)
[D38999/24MD35BA](#) [D38999/24SA35BN](#) [D38999/24SC35BA](#) [D38999/24SC35BB](#) [D38999/24SC98BA](#)
[D38999/24SC35BC](#) [D38999/24SC35BD](#) [D38999/24SC35BE](#) [D38999/24MC4PB](#) [D38999/24KF32PD](#) [TVS07RF-17-](#)
[35PA](#) [D38999/24SF32PB](#) [D38999/24WJ61PE](#) [D38999/24KC98SB](#) [TVS07RF-17-35SB](#) [TVS07RF-23-35SE](#)
[TVS07RF-25-11P](#) [TVS07RF-25-11PA](#) [TVS07RF-25-11PA-LC](#) [TVS07RF-25-11PB](#) [TVS07RF-25-11PC](#) [TVS07RF-25-](#)
[11PC-LC](#) [TVS07RF-25-11PD](#) [TVS07RF-25-11PD-LC](#) [TVS07RF-25-11PE](#) [TVS07RF-25-11PE-LC](#) [TVS07RF-25-11P-](#)
[LC](#) [TVS07RF-25-11S](#) [TVS07RF-25-11SA](#) [TVS07RF-25-11SA-LC](#) [TVS07RF-25-11SB](#) [TVS07RF-25-11SB-LC](#)
[TVS07RF-25-11SC](#) [TVS07RF-25-11SC-LC](#) [TVS07RF-25-11SD](#) [TVS07RF-25-11SD-LC](#) [TVS07RF-25-11SE](#)
[TVS07RF-25-11SE-LC](#) [TVS07RF-25-11S-LC](#) [TVS07RF-25-20P](#) [TVS07RF-25-20PA](#) [TVS07RF-25-20PA-LC](#)
[TVS07RF-25-20PB](#) [TVS07RF-25-20PC](#) [TVS07RF-25-20PC-LC](#) [TVS07RF-25-20PD](#) [TVS07RF-25-20PD-LC](#)
[TVS07RF-25-20PE](#) [TVS07RF-25-20PE-LC](#)