


REV.	DATE	DESCRIPTION
NC	09/25/06	INITIAL RELEASE



8					<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"</div> <div>DO NOT SCALE DRAWING</div>	APPROVALS		DATE		<div>Amphenol Connex</div>				
7	GASKET	RUBBER	RED	1		DRAWN	G.R.S.	09/25/06						
6	RETAINING RING	BRASS	NICKEL	1		CHECKED								
5	RING	DELRIN	NATURAL	1		ISSUED			PART DESCRIPTION <div>SMA JACK TO TNC REVERSE POLARITY JACK ADAPTER</div>					
4	WASHER	BRASS	NICKEL	1		SHEET	1 OF 1							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1				PART NO. <div>242105RP-10</div>						
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NICKEL	1				DWG. NO. 242105RP-10.DWG						
DESCRIPTION		MATERIAL	FINISH	QTY		C:/242/242105RP-10.DWG							REV.	NC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242105RP-10](#)