


RoHS Compliant


Rev.	SIGN	DATE	DESCRIPTION	APPROVER
A0		2023.10.20		Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



Technical Specification:

1. Current: 35A.
2. Torque: 13 lbf.in.
3. Mark"▲" is the Critical dimension.

⑥	Spacer	Steel , Matte Tin Plated	1PCS
⑤	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

<div>Amphenol</div> <div>ANYTEK</div>				<div>CUSTOMER COPY</div> <div>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES I N ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR.PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</div>				
TITLE		AMT44007DB terminal						
PART NO.		AMT0440007DB0000G		DWG NO.	8AMT0011			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Guoxue 2023.10.20	Guoxue 2023.10.20			UNIT: mm		≥30 ±0.60
						SCALE: NONE		6-30 ±0.40
						REV.: A0		0-6 ±0.30
				SHEET: 01/01		ANGLES ±1°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0440007DB0000G](#)