




RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
A0		2023.10.20		Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Technical Specification:
1. Current: 40A.
2. Torque: 13 lbf.in.
3. Mark "▲" is the Critical dimension.



⑥	Spacer	Steel , Matte Tin Plated	1PCS
①	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

<div>Amphenol</div> <div>ANYTEK</div>				<div>CUSTOMER COPY</div> <div>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</div>						
TITLE		AMT44012DB terminal								
PART NO.		AMT0440012DB0000G		DWG NO.		8AMT0014				
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance		
			Guoxue 2023.10.20	Guoxue 2023.10.20				UNIT: mm		>30 ±0.60
						SCALE: NONE				6-30 ±0.40
						SHEET: 01/01		REV.: A0		0-6 ±0.30
										ANGLES ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0440012DB0000G](#)