




RoHS Compliant


Rev.	SIGN	DATE	DESCRIPTION	APPROVER
A0		2023.10.20		Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Technical Specification:

1. Current: 40A.
2. Torque: 13 lbf.in.
3. Mark "▲" is the Critical dimension.



⑥	Spacer	Steel , Matte Tin Plated	1PCS
⑤	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

<div>Amphenol</div> <div>ANYTEK</div>				<div>CUSTOMER COPY</div> <div>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</div>			
TITLE		AMT44020DB terminal					
PART NO.		AMT0440020DB0000G		DWG NO.		8AMT0015	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Guoxue 2023.10.17	Guoxue 2023.10.17	<div></div> <div>SHEET: 01/01</div>		<div>UNIT: mm</div> <div>SCALE: NONE</div> <div>REV.: A0</div>
							<div>>30 ±0.60</div> <div>6-30 ±0.40</div> <div>0-6 ±0.30</div> <div>ANGLES ±1°</div>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0440020DB0000G](#)