






RoHS Compliant



- Technical Specification:
- Current: 100A.
 - Torque: 15 lbf.in.
 - Mark"▲" is the Critical dimension.



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM
WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR.
PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

①	Spacer	Steel, Matte Tin Plated	1PCS
②	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q'ty
TITLE AMT45017DB Stamped terminal			
PART NO.	AMT0450017DB0000G		DWG NO. 8AMT0024
APPROVED	CHECKED	DESIGNED	DRAWN
		Seamus 2023.10.16	Seamus 2023.10.16
		UNIT: mm	Tolerance
		SCALE: NONE	>30 ±0.60
		REV.: A0	0-6 ±0.40
			ANGLES ±1°

PCB Layout

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0450017DB0000G](#)